




Decoilers



Decoiler K1-CW



Decoiler K1-CW/AQ



NEW

K1-CW/AQ/LSE/S



K1-LAQ



Lifting Traverse K1-CWT

Mobile Decoiler K1-CW

| | Item No.: | width | coil-width | max. |
|------------------|-----------|---------|----------------|---------|
| K1-CW/100 | 91201 | 1000 mm | 800 mm | 2000 kg |
| K1-CW/125 | 91202 | 1250 mm | 1000 mm | 1500 kg |
| K1-CW/150 | 91205 | 1500 mm | 1250 mm | 1500 kg |

- ¾ decoiler K1-CW with core, two steering and two parking castors
- ¾ core has **five** adjustable arms, avoiding marks, dents or scratch marks, when the coil is clamped or decoiled
- ¾ core I.D. K1-CW/100: Ø 230-510 mm
- ¾ core I.D. K1-CW/125: Ø 250-515 mm
- ¾ core I.D. K1-CW/150: Ø 360-650 mm

Mobile Decoiler K1-CW/AQ including Decoiling & Cross Cut Attachment

| | Item: | width | coil-width | max. |
|--------------------|-------|---------|----------------|---------|
| K1-CW/100AQ | 91241 | 1000 mm | 800 mm | 2000 kg |
| K1-CW/125AQ | 91242 | 1250 mm | 1000 mm | 1500 kg |
| K1-CW/150AQ | 91245 | 1500 mm | 1250 mm | 1500 kg |

Technical details decoiler see K1-CW ñ

Technical details cross cut attachment AQ see also next page [

- | max. cutting capacity: 1,0 mm, stainl. : 0,5 mm
- | max. transport (unroll) capacity AQ : 750 kg
- | max coil outside diameter: 800 mm

Mobile Decoiler K1-CW/AQ/LSE/S cpl. including Decoiling & Cross Cut Attachment and cpl. length cut Slitter Device.

Ideal for mobile on site cutting & slitting

| | Item No | width | coil-width |
|--------------------------|---------|---------|----------------|
| K1-CW/100AQ/LSE/S | 91271 | 1000 mm | 800 mm |
| K1-CW/125AQ/LSE/S | 91272 | 1250 mm | 1000 mm |
| K1-CW/150AQ/LSE/S | 91275 | 1500 mm | 1250 mm |

Incl. Cordless Metal Shear Set AK3514-2 for length cut slitting

Easy to move, easy to transport, easy to decoil, easy to cut. Cross- and length wise cutting on site or in the workshop

Technical details decoiler see K1-CW ñ

Technical details cross cut attachment AQ see also next page [

Mechanical measuring device K1-LAQ

| | Item No.: | max. length | preciseness |
|---------------|-----------|-------------|-------------|
| K1-LAQ | 91260 | 999,99 m | ½ cm |

Lifting Traverse K1-CWT

| | Item No.: | capacity |
|---------------|-----------|----------|
| K1-CWT | 91230 | 2000 kg |


certified VGB 9a UVV 18 DIN 18800 for coil width up to 1000 mm

Decoilers and Cores are also available in special dimensions. Inform us about your requirements.

Decoiling & Cross Cut Attachment K1 – AQ

The Slitter Attachment K1-AQ can be fitted to any DRACO Decoiler or can be mounted on to a workbench. When ordering, please state item and type number on decoiler label.

| | Item No.: | width | Adv. coil-width |
|-----------------|-----------|---------|-----------------|
| K1-100AQ | 91251 | 1000 mm | 800 mm |
| K1-125AQ | 91252 | 1250 mm | 1000 mm |
| K1-150AQ | 91255 | 1500 mm | 1250 mm |



Decoiling & Cross Cut Attachment K1-AQ
(Pic. incl. opt. measuring device)



Slitter attachment K1-LSE for decoiler or workbench

Technical details, cutting capacity:

| | | |
|--------------------------------|----|-----|
| aluminium, copper, zinc | mm | 1,0 |
| galvanised steel | mm | 1,0 |
| stainless steel | mm | 0,5 |
| pull capacity ± | kg | 750 |
| weight of slitter attachment ± | kg | 30 |

- ¾ rubber transportation rolls for a better grip
- ¾ wheel for forward & reverse transportation of the coil-material with clamping device
- ¾ collars adjustable for coil width
- ¾ cutting rolls can be re-sharpened
- ¾ ball bearings are maintenance free

Lengths cut slitter device K1-LSE

| | Item No.: | without shear |
|------------------|-----------|---------------|
| K1-LSE100 | 91268 | for K1-100AQ |
| K1-LSE125 | 91269 | for K1-125AQ |
| K1-LSE150 | 91270 | for K1-150AQ |

for all Shears Series 20.. and 35.. with mounting hole



K1-CSg

Quick-Strap K1-CSg

| | Item No.: | measurements mm |
|---------------|-----------|-----------------|
| K1-CSg | 91277 | ± 2500 x 48 |

No more damaged coils. The 2500 x 48 mm wide strap eliminates damage caused by wire, string, rope or tape. Quick fastening and release using Velcro fastening and is ideal for work-shops and site- work, also for safe transporting of coils, to and from the site.



K1-AGb

K1-AG with K1-AGb

Coil Trolley K1-AG

- ¾ easy transportation without danger of coils up to 1500 mm width
- ¾ simple & easy decoiling

| | Item No.: | capacity | kg |
|-----------------|-----------|----------|----|
| K1-AG | 91280 | 250 kg | 24 |
| K1-AG125 | 91281 | 250 kg | 26 |

Guide K1-AGb for Coil Trolley

| | Item No.: | coil width mm | kg |
|------------------|-----------|---------------|-----|
| K1-AGb | 91285 | 0 –1500 | 4,5 |
| K1-AGb125 | 91286 | bis 1150 mm | 5,0 |